

Orders on request only



- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

General ordering data

Version	Automatic stripper and crimper
Order No.	9205790000
Type	CA 100/10
GTIN (EAN)	4032248813285
Qty.	1 items

CA 100/10

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	400 mm	Depth (inches)	15.748 inch
Height	460 mm	Height (inches)	18.1102 inch
Width	530 mm	Width (inches)	20.8661 inch
Net weight	48000 g		

Environmental Product Compliance

RoHS Compliance Status Compliant
 REACH SVHC Lead 7439-92-1

PW65 maintenance - automatic stripping/crimping

Stripping range	Only for 10,0 mm ² wire end ferrule with collar	Drive	Electropneumatic
Pulse time	approx. 1.5 s	Crimping	Trapezoidal
Crimping length	12 - 18 mm	Consumables	loose cable lugs, With and without plastic collar
Compressed-air connection	5 bar	Electrical connection	100-240 V / 50/65 Hz

Classifications

ETIM 8.0	EC002778	ETIM 9.0	EC002778
ETIM 10.0	EC002778	ECLASS 14.0	17-13-01-01
ECLASS 15.0	17-13-01-01		