

MULTIMETER C 2608

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	108 mm	Depth (inches)	4.252 inch
Height	53 mm	Height (inches)	2.0866 inch
Width	281 mm	Width (inches)	11.063 inch
Net weight	888.2 g		

Environmental Product Compliance

RoHS Compliance Status Compliant
 REACH SVHC Lead 7439-92-1

Technical data

Description of article Digital clamp-on measuring device

Measuring and testing devices

Measured capacitance value, max.	6.6 mF	Measured capacitance value, min.	6.6 nF
Selection of measuring range	Manual	Measuring range category	CAT III
Opening width of current-measuring clamp-on attachment	57 mm	AC voltage measuring range	0.66 - 750 V
DC voltage measuring range	0.66 - 1000 V	Measured current value, max.	2000 A
Working temperature, max.	50 °C	Working temperature, min.	0 °C
Frequency range, max.	66 Hz	Frequency range, min.	1 MHz
Frequency measurement	Yes	Display	digital
Type of current	AC, DC	Resistance measuring range, max.	66 MΩ
Resistance measuring range, min.	660 Ω	Resolution of DC voltage	± 0.5%
Resolution of AC voltage	± 0.5%	Battery type	9V block battery
Tested and approved according to	EN/IEC 61010-1		

Important note

Product information Min/max function only applies for the DC range.

Classifications

ETIM 8.0	EC000380	ETIM 9.0	EC000380
ETIM 10.0	EC000380	ECLASS 14.0	27-20-03-12
ECLASS 15.0	27-20-03-12		

MULTIMETER C 2608

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

Example of use

