

RCLS3T024W

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Product image



Individual relays for TERMSERIES

- Electromechanical relays
- Different contact materials

General ordering data

Version	TERMSERIES, Relay, Number of contacts: 1, NO contact AgSnO + W, Rated control voltage: 24 V DC, Continuous current: 16 A, Plug-in connection, Test button available: No
Order No.	8866920000
Type	RCLS3T024W
GTIN (EAN)	4032248606528
Qty.	20 items

RCLS3T024W

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E522350

Dimensions and weights

Depth	15.7 mm	Depth (inches)	0.6181 inch
Height	29 mm	Height (inches)	1.1417 inch
Width	12.7 mm	Width (inches)	0.5 inch
Net weight	15.15 g		

Temperatures

Storage temperature	-40 °C...85 °C	Ambient temperature	-25 °C...70 °C
Operating temperature		Humidity	40 °C / 93 % rel. humidity, no condensation

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Rated data UL

Certificate No. (cURus) E522350

Control side

Rated control voltage	24 V DC	Rated current DC	16.7 mA
Power rating	400 mW	Status indicator	No

Load side

Rated switching voltage	250 V AC	Continuous current	16 A
Max. switching frequency at rated load	0.1 Hz	Inrush current	165 A / 20 ms, 800 A / 200 µs
AC switching capacity (resistive), max.	4000 VA	DC switching capacity (resistive), max.	384 W @ 24 V
Switch-on delay	≤ 10 ms	Switch-off delay	≤ 6 ms
Contact type	1 NO contact (AgSnO + W)	Mechanical service life	5 x 10 ⁶ switching cycles
Min. switching power	1 W		

General data

Test button available	No	Mechanical switch position indicator	No
Colour	white	UL 94 flammability rating	V-0

Insulation coordination

Rated voltage	250 V	Pollution severity	2
Surge voltage category	III	Insulating material group	IIIa

RCLS3T024W

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Clearance and creepage distances for control side - load side	≥ 10 mm	Dielectric strength for control side - load side	5 kVeff / 1min
Dielectric strength of open contact	1 kVeff / 1 min	Protection degree	IP20

Further details of approvals / standards

Certificate No. (CSA)	249409-2426937	Certificate No. (VDE)	40020589
Certificate No. (cURus)	E522350		

Connection data


Wire connection method	Plug-in connection	Pitch in mm (P)	5.00 mm
------------------------	--------------------	-----------------	---------

Classifications

ETIM 8.0	EC001437	ETIM 9.0	EC001437
ETIM 10.0	EC001437	ECLASS 14.0	27-37-16-01
ECLASS 15.0	27-37-16-01		


Drawings

Wiring diagram




View of Pins from below

Graph



DC load limit curve

Dimensional drawing




RCLS3T024W

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

Drawings

www.weidmueller.com

Miscellaneous



Type codes

RCLS3T024W

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

Counterpart

www.weidmueller.com

Screw connection



TERMSERIES empty sockets with:

- 1 CO contact
- Unique multi-voltage input from 24 to 230 V UC
- Input voltages from 5 V DC to 230 V UC with coloured marking: AC: red, DC: blue, UC: white
- Due to high-quality design and no sharp edges no risk of injuries during installation
- Partition plates for optical separation and reinforcement of insulation

General ordering data

Type	TOS 24VDC EMPTY	Version
Order No.	1127720000	TERMSERIES, Relay socket, Rated control voltage: 24 V DC $\pm 20\%$,
GTIN (EAN)	4032248909377	Rated switching voltage: 230 V AC, Continuous current: 16 A, Screw
Qty.	10 ST	connection

Tension clamp connection



TERMSERIES empty sockets with:

- 1 CO contact
- Unique multi-voltage input from 24 to 230 V UC
- Input voltages from 5 V DC to 230 V UC with coloured marking: AC: red, DC: blue, UC: white
- Due to high-quality design and no sharp edges no risk of injuries during installation
- Partition plates for optical separation and reinforcement of insulation

General ordering data

Type	TOZ 24VDC EMPTY	Version
Order No.	1127740000	TERMSERIES, Relay socket, Rated control voltage: 24 V DC $\pm 20\%$,
GTIN (EAN)	4032248909421	Rated switching voltage: 230 V AC, Continuous current: 16 A,
Qty.	10 ST	Tension-clamp connection

Screw connection



TERMSERIES empty sockets with:

- 1 CO contact
- Unique multi-voltage input from 24 to 230 V UC
- Input voltages from 5 V DC to 230 V UC with coloured marking: AC: red, DC: blue, UC: white
- Due to high-quality design and no sharp edges no risk of injuries during installation
- Partition plates for optical separation and reinforcement of insulation

General ordering data

Type	TOS 24-230VUC EMPTY	Version
Order No.	1127730000	TERMSERIES, Relay socket, Rated control voltage: 24...230 V UC $\pm 10\%$,
GTIN (EAN)	4032248909254	Rated switching voltage: 230 V AC, Continuous current: 16 A,
Qty.	10 ST	Screw connection

RCLS3T024W

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Counterpart

Tension clamp connection



TERMSERIES empty sockets with:

- 1 CO contact
- Unique multi-voltage input from 24 to 230 V UC
- Input voltages from 5 V DC to 230 V UC with coloured marking: AC: red, DC: blue, UC: white
- Due to high-quality design and no sharp edges no risk of injuries during installation
- Partition plates for optical separation and reinforcement of insulation

General ordering data

Type	TOZ 24-230VUC EMPTY	Version	
Order No.	1127750000	TERMSERIES, Relay socket, Rated control voltage: 24...230 V UC ±10	
GTIN (EAN)	4032248909223	% , Rated switching voltage: 230 V AC, Continuous current: 16 A,	
Qty.	10 ST	Tension-clamp connection	

PUSH IN connection



TERMSERIES empty sockets with:

- 1 CO contact
- Unique multi-voltage input from 24 to 230 V UC
- Input voltages from 5 V DC to 230 V UC with coloured marking: AC: red, DC: blue, UC: white
- Due to high-quality design and no sharp edges no risk of injuries during installation
- Partition plates for optical separation and reinforcement of insulation

General ordering data

Type	TOP 24VDC EMPTY	Version	
Order No.	2618740000	TERMSERIES, Relay socket, Rated control voltage: 24 V DC ±20 % ,	
GTIN (EAN)	4050118670097	Rated switching voltage: 230 V AC, Continuous current: 16 A, PUSH	
Qty.	10 ST	IN	
Type	TOP 24-230VUC EMPTY ED2	Version	
Order No.	2663110000	TERMSERIES, Relay socket, Rated control voltage: 24...230 V UC ±10	
GTIN (EAN)	4050118697964	% , Rated switching voltage: 250 V AC, Continuous current: 16 A,	
Qty.	10 ST	PUSH IN	

Screw connection



TERMSERIES empty sockets with:

- 1 CO contact
- Unique multi-voltage input from 24 to 230 V UC
- Input voltages from 5 V DC to 230 V UC with coloured marking: AC: red, DC: blue, UC: white
- Due to high-quality design and no sharp edges no risk of injuries during installation
- Partition plates for optical separation and reinforcement of insulation

Counterpart

General ordering data

Type	TOS 24-230VUC EMPTY ED2	Version
Order No.	2662950000	TERMSERIES, Relay socket, Rated control voltage: 24...230 V UC ±10
GTIN (EAN)	4050118698121	% , Rated switching voltage: 250 V AC, Continuous current: 16 A,
Qty.	10 ST	Screw connection