

## RSM-16 C 1CO S


**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

Digital output interface per-relay for electrical signal transmission between the PLC and the field.

- Electrical isolation by pluggable relays.
- Integrated LED status display.
- Screw or tension clamp-connection.
- Additional functions: in-series fuse or isolator
- 2 versions available: compact (RSS relay) or standard (RCL relay).

### General ordering data

|            |   |
|------------|---|
| Version    | Interface, RSM, 16 compact, RCL, Screw connection |
| Order No.  | <a href="#">9445 100000</a>                       |
| Type       | RSM-16 C 1CO S                                    |
| GTIN (EAN) | 4032248150960                                     |
| Qty.       | 1 items   |

## RSM-16 C 1CO S

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

## Dimensions and weights

|            |          |                 |             |
|------------|----------|-----------------|-------------|
| Depth      | 73 mm    | Depth (inches)  | 2.874 inch  |
| Height     | 109 mm   | Height (inches) | 4.2913 inch |
| Width      | 185 mm   | Width (inches)  | 7.2835 inch |
| Net weight | 569.36 g |                 |             |

## Temperatures

|                     |             |                       |             |
|---------------------|-------------|-----------------------|-------------|
| Storage temperature | -40...60 °C | Operating temperature | -25...40 °C |
|---------------------|-------------|-----------------------|-------------|

## Environmental Product Compliance

|                                      |   |
|--------------------------------------|---|
| RoHS Compliance Status               | Compliant with exemption                            |
| RoHS Exemption (if applicable/known) | 7a, 7cI   |
| REACH SVHC                           | Lead 7439-92-1, 4,4'-isopropylidenediphenol 80-05-7 |
| SCIP                                 | 66e752f3-a24f-4fef-89c4-f29f52d01390                |

## General data

|                                  |        |                   |        |
|----------------------------------|--------|-------------------|--------|
| LED status display per relay     | green  | Fuse per relay    | No     |
| LED status of the supply voltage | yellow | Power supply fuse | 3.15 A |

## Connection data

|                                |              |                            |   |
|--------------------------------|--------------|----------------------------|---|
| Number of poles (control side) | 20-pole plug | Connection supply          | LL 5.08 mm  |
| Connection (field side)        | LL2N 5.08 mm | Connection on control side | Plug-in connector in acc. with IEC60603-13 / DIN41651 |

## Rating data

|                         |                                      |
|-------------------------|--------------------------------------|
| Mechanical service life | 3 x 10 <sup>7</sup> switching cycles |
|-------------------------|--------------------------------------|

## Ratings data input

|               |               |               |       |
|---------------|---------------|---------------|-------|
| Input voltage | 24 V DC ± 10% | Input current | 20 mA |
| Power rating  | 0.4 VA        |               |       |

## Ratings data output

|                            |            |                         |                        |
|----------------------------|------------|-------------------------|------------------------|
| Relay type                 | RCL        | Type of output          | Potential-free contact |
| Material of contacts       | AgNi 90/10 | Rated voltage           | ≤ 250 Vdc ≤ 250 Vac    |
| Max. AC continuous current | 5 A        | AC peak current         | 16 A                   |
| Minimum contact current    | 0.01 A     | Minimum contact voltage | 10 V                   |

**RSM-16 C 1CO S**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Insulation coordinates (EN50178)**

|                                   |              |                                    |           |
|-----------------------------------|--------------|------------------------------------|-----------|
| According to                      | DIN EN 50178 | Rated input insulation voltage     | <50 V AC  |
| Rated output insulation voltage   | <250 V AC    | Overvoltage category input/input   | III       |
| Overvoltage category input/output | III          | Overvoltage category output/output | II        |
| Pollution severity level          | 2            | Pulse voltage test (1,2/50µs)      | 6 kV      |
| Insulation test voltage AC        | 1.2 kV       | Clearance input/output             | ≥ 5.5 mm  |
| Clearance input/input             | ≥ 0.2 mm     | Clearance output/output            | ≥ 1.17 mm |

**Connection field**

|                                  |                     |                            |                      |
|----------------------------------|---------------------|----------------------------|----------------------|
| Min. wire cross-section, AWG     | AWG 26              | Type of connection         | Screw connection     |
| Sleeve with plastic collar, max. | 2.5 mm <sup>2</sup> | Flexible with sleeve, min. | 0.5 mm <sup>2</sup>  |
| Flexible with sleeve, max.       | 2.5 mm <sup>2</sup> | Flexible, max. H05(07) V-K | 4 mm <sup>2</sup>    |
| Flexible, min. H05(07) V-K       | 0.5 mm <sup>2</sup> | Solid, max. H05(07) V-U    | 6 mm <sup>2</sup>    |
| Solid, min. H05(07) V-U          | 0.5 mm <sup>2</sup> | Stripping length           | 6 mm                 |
| Tightening torque, max.          | 0.6 Nm              | Tightening torque, min.    | 0.5 Nm               |
| Clamping range, max.             | 6 mm <sup>2</sup>   | Clamping range, min.       | 0.13 mm <sup>2</sup> |
| Max. wire cross-section, AWG     | AWG 12              |                            |                      |

**Supply connection**

|                              |                     |                                   |                      |
|------------------------------|---------------------|-----------------------------------|----------------------|
| Type of connection           | Screw connection    | Clamping range, min.              | 0.13 mm <sup>2</sup> |
| Clamping range, max.         | 6 mm <sup>2</sup>   | Solid, min. H05(07) V-U           | 0.5 mm <sup>2</sup>  |
| Solid, max. H05(07) V-U      | 6 mm <sup>2</sup>   | Flexible, min. H05(07) V-K        | 0.5 mm <sup>2</sup>  |
| Flexible, max. H05(07) V-K   | 4 mm <sup>2</sup>   | Flexible with sleeve, max.        | 2.5 mm <sup>2</sup>  |
| Flexible with sleeve, min.   | 0.5 mm <sup>2</sup> | Ferrule with plastic collar, max. | 2.5 mm <sup>2</sup>  |
| Wire cross-section, min. AWG | AWG 26              | Wire cross-section, max. AWG      | AWG 12               |
| Tightening torque, min.      | 0.5 Nm              | Tightening torque, max.           | 0.6 Nm               |
| Stripping length             | 6 mm                |                                   |                      |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002780    | ETIM 9.0    | EC002780    |
| ETIM 10.0   | EC002780    | ECLASS 14.0 | 27-14-11-52 |
| ECLASS 15.0 | 27-14-11-52 |             |             |

