


RSM-16 2CO S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Digital output interface per-relay for electrical signal transmission between the PLC and the field.

- Electrical isolation by pluggable relays.
- Integrated LED status display.
- Screw or tension clamp-connection.
- Additional functions: in-series fuse or isolator
- 2 versions available: compact (RSS relay) or standard (RCL relay).

General ordering data

Version	Interface, RSM, 16 2CO, RCL, Screw connection
Order No.	9445160000
Type	RSM-16 2CO S
GTIN (EAN)	4032248252855
Qty.	1 items
Delivery status	Discontinued

RSM-16 2CO S

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	68 mm	Depth (inches)	2.6772 inch
Height	109 mm	Height (inches)	4.2913 inch
Width	263 mm	Width (inches)	10.3543 inch
Net weight	718 g		

Temperatures

Storage temperature	-40...60 °C	Operating temperature	-25...40 °C
---------------------	-------------	-----------------------	-------------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	7a, 7cl
REACH SVHC	Lead 7439-92-1
SCIP	71d9bdc4-a0b5-4af0-93bd-2ad4e523fb14

General data

LED status display per relay	green	Fuse per relay	No
LED status of the supply voltage	yellow	Power supply fuse	3.15 A

Connection data

Number of poles (control side)	20-pole plug	Connection supply	LP 5.08mm
Connection (field side)	LP2N 5.08mm	Connection on control side	Plug-in connector in acc. with IEC60603-13 / DIN41651

Rating data

Mechanical service life	3 x 10 ⁷ switching cycles
-------------------------	--------------------------------------

Ratings data input

Input voltage	24 V DC ± 10%	Input current	17 mA
Power rating	0.4 VA		

Ratings data output

Relay type	RCL	Type of output	Potential-free contact
Material of contacts	AgNi 90/10	Rated voltage	≤ 250 Vdc ≤ 250 Vac
Max. AC continuous current	4 A	AC peak current	16 A
Minimum contact current	0.01 A	Minimum contact voltage	10 V

RSM-16 2CO S

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Insulation coordinates (EN50178)

According to	DIN EN 50178	Rated input insulation voltage	< 50 V AC
Rated output insulation voltage	< 250 V AC	Overvoltage category input/input	III
Overvoltage category input/output	III	Overvoltage category output/output	II
Pollution severity level	2	Pulse voltage test (1,2/50µs)	6 kV
Insulation test voltage AC	2.5 kV	Clearance input/output	≥ 5.5 mm
Clearance input/input	≥ 0.2 mm	Clearance output/output	≥ 1.17 mm

Connection field

Min. wire cross-section, AWG	AWG 26	Type of connection	Screw connection
Sleeve with plastic collar, max.	2.5 mm ²	Flexible with sleeve, min.	0.5 mm ²
Flexible with sleeve, max.	2.5 mm ²	Flexible, max. H05(07) V-K	4 mm ²
Flexible, min. H05(07) V-K	0.5 mm ²	Solid, max. H05(07) V-U	6 mm ²
Solid, min. H05(07) V-U	0.5 mm ²	Stripping length	6 mm
Tightening torque, max.	0.6 Nm	Tightening torque, min.	0.5 Nm
Clamping range, max.	6 mm ²	Clamping range, min.	0.13 mm ²
Max. wire cross-section, AWG	AWG 12		

Supply connection

Type of connection	Screw connection	Clamping range, min.	0.13 mm ²
Clamping range, max.	6 mm ²	Solid, min. H05(07) V-U	0.5 mm ²
Solid, max. H05(07) V-U	6 mm ²	Flexible, min. H05(07) V-K	0.5 mm ²
Flexible, max. H05(07) V-K	4 mm ²	Flexible with sleeve, max.	2.5 mm ²
Flexible with sleeve, min.	0.5 mm ²	Ferrule with plastic collar, max.	2.5 mm ²
Wire cross-section, min. AWG	AWG 26	Wire cross-section, max. AWG	AWG 12
Tightening torque, min.	0.5 Nm	Tightening torque, max.	0.6 Nm
Stripping length	6 mm		

Classifications

ETIM 8.0	EC002780	ETIM 9.0	EC002780
ETIM 10.0	EC002780	ECLASS 14.0	27-14-11-52
ECLASS 15.0	27-14-11-52		

