

IE-FM6D2UE0003MST0ST0X

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Assembled IE cables, FO breakout cable, multimode, SC duplex - SC duplex, black, Core diameter 62.5 µm

General ordering data

| | |
|------------|---|
| Version | Dragline cable, ST, ST IP 20, 62.5 µm, PUR, 3 m |
| Order No. | 8876460030 |
| Type | IE-FM6D2UE0003MST0ST0X |
| GTIN (EAN) | 4032248610044 |
| Qty. | 1 items |

IE-FM6D2UE0003MST0ST0X

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|-------|-----------------|---------------|
| Length | 3 m | Length (inches) | 118.1102 inch |
| Net weight | 100 g | | |

Temperatures

| | | | |
|--------------------------|----------------|-----------------------|----------------|
| Storage temperature | -40 °C...80 °C | Operating temperature | -40 °C...80 °C |
| Installation temperature | -20 °C...60 °C | | |

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 67cf1078-beca-4687-860b-dc475a6ec24a |

General standards

| | |
|--------------------|-------------|
| Connector standard | IEC 61754-2 |
|--------------------|-------------|

Standards

| | |
|--------------------|-------------|
| Connector standard | IEC 61754-2 |
|--------------------|-------------|

Fibre-optic

| | | | |
|----------------|---|---------------------------|---|
| Fibre type | GOF, Multimode, OM1 | Attenuation | 2.7 dB/km at 850 nm, ≤ 0.5 dB/km at 1300 nm |
| Insertion loss | ≤ 0.4 dB | Return loss (attenuation) | ≥ 30 dB |
| Bandwidth | 200 MHz*km at 850 nm, 500 MHz*km at 1300 nm | | |

Cable structure

| | | | |
|-----------------|-----------|------------------|--------------------|
| Sheath diameter | 6 mm | Sheathing colour | black |
| Material sheath | PUR | Cable layout | Break-out dragline |
| Primary coating | 245.00 µm | Core diameter | 62.5 µm |

Mechanical and material properties of cable

| | | | |
|--------------------------------|-------|---------------------------------|---------|
| Halogen | No | Min. bending radius, repetitive | 77 mm |
| Min. bending radius, once only | 25 mm | Bending cycles | 100,000 |

Plug

| | | | |
|------------|---|-----------|---|
| Plug right | ST, IP20, male contact, straight, plug, Plastic, unshielded | Plug left | ST, IP20, male contact, straight, plug, Plastic, unshielded |
|------------|---|-----------|---|

IE-FM6D2UE0003MST0ST0X

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Plug, left**

| | |
|-----------|---|
| Plug left | ST, IP20, male contact, straight, plug, Plastic, unshielded |
|-----------|---|

Plug, right

| | |
|------------|---|
| Plug right | ST, IP20, male contact, straight, plug, Plastic, unshielded |
|------------|---|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002607 | ETIM 9.0 | EC002607 |
| ETIM 10.0 | EC002607 | ECLASS 14.0 | 27-06-10-03 |
| ECLASS 15.0 | 27-06-10-03 | | |

Detailed drawing

