

JPO 24VDC 2X0.2A M12S

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Weidmüller is now one of the industry's leading international providers of connectors. An important mainstay in this product family are the circular connectors, which Weidmüller groups under the product name SAI. In the development of SAI products, Weidmüller engineers have always concentrated on achieving rational, cost-effective installation concepts, and – in cooperation with major users – have supplied the markets with well-conceived products which set standards in terms of functionality and quality across the globe. An example is the Jackpac® product family. These modules are waterproof signal converters.

General ordering data

Version	JACKPAC, Level converter, Rated control voltage: 18...24...30 V DC , Rated switching voltage: 3...33 V DC, M12 plug / plug, A-coded
Order No.	8929960000
Type	JPO 24VDC 2X0.2A M12S
GTIN (EAN)	4032248706013
Qty.	1 items
Delivery status	This article will no longer be available in the future.
Available until	2025-11-30T00:00:00+01:00

JPO 24VDC 2X0.2A M12S

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Height	14.4 mm	Height (inches)	0.5669 inch
Width	36 mm	Width (inches)	1.4173 inch
Net weight	50 g		

Temperatures

Storage temperature	Operating temperature	-20 °C...60 °C
---------------------	-----------------------	----------------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	7a
REACH SVHC	Lead 7439-92-1
SCIP	1b05ef5c-aeab-43a7-8ce0-9a79e97b9996

Input

Rated control voltage	18...24...30 V DC	Rated control voltage	18 V...24 V...30 V DC
-----------------------	-------------------	-----------------------	-----------------------

Control side

Rated control voltage	18...24...30 V DC	Nominal control current	7 mA DC
-----------------------	-------------------	-------------------------	---------

Output

Rated switching voltage	3...33 V DC
-------------------------	-------------

Load side

Rated switching voltage	3...33 V DC	Rated switching current	200 mA
-------------------------	-------------	-------------------------	--------

Insulation coordination

Rated voltage	32 V	Surge voltage category	I
Pollution severity	2	Protection degree	IP67

Insulation coordination

Rated voltage	32 V	Pollution severity	2
Surge voltage category	I	Protection degree	IP67

output

Switching voltage, max.	3...33 V DC
-------------------------	-------------

JPO 24VDC 2X0.2A M12S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Technical specifications for cable

Shielded	No
----------	----

Important note

Product information	Length of connected cable smaller than 30m
---------------------	--

Classifications

ETIM 8.0	EC001134	ETIM 9.0	EC001134
ETIM 10.0	EC001134	ECLASS 14.0	19-17-90-90
ECLASS 15.0	19-17-90-90		

JPO 24VDC 2X0.2A M12S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

