



- supplied loose in polybag
- Weidmüller colour code
- DIN colour code
- other colour code

### General ordering data

|            |   |
|------------|---|
| Version    | Wire-end ferrule, Standard, 21 mm, 18 mm, red |
| Order No.  | <a href="#">9019250000</a>                    |
| Type       | H10,0/28D R                                   |
| GTIN (EAN) | 4008 19004 1410                               |
| Qty.       | 100 items                                     |
| Packaging  | loose   |

Technical data

Approvals

Approvals



|                         |                            |
|-------------------------|----------------------------|
| ROHS                    | Conform                    |
| UL File Number Search   | <a href="#">UL Website</a> |
| Certificate no. (cULus) | E499744                    |

Dimensions and weights

|            |        |
|------------|--------|
| Net weight | 0.62 g |
|------------|--------|

Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

Technical data

| Description of article | Wire end ferrule with plastic collar, red | Version | Standard |
|------------------------|---|---------|----------|
|------------------------|---|---------|----------|

Wire-end ferrules

|                               |          |   |                    |
|-------------------------------|----------|---|--------------------|
| Contact surface diameter (D1) | 4.5 mm   | Contact surface length (L2)             | 18 mm              |
| Collar diameter (D2)          | 7.6 mm   | Plastic collar thickness (S2)           | 0.4 mm             |
| L1 in mm                      | 28.00 mm | Wire connection cross section AWG, max. | AWG 8              |
| Metal sleeve thickness (S1)   | 0.2 mm   | Military designation                    | T 20A 025 A        |
| Stripping length              | 21 mm    | Conductor cross-section                 | 10 mm <sup>2</sup> |
| Colour code                   | DIN      |   |                    |

Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000005    | ETIM 9.0    | EC000005    |
| ETIM 10.0   | EC000005    | ECLASS 14.0 | 27-40-02-01 |
| ECLASS 15.0 | 27-40-02-01 |             |             |

Drawing

