


H2,5/16DS BL



- Polypropylene conical cable entry funnel
 - Heat-resistant up to 105°C
- For conductors from 0.5 – 10.0 mm² (AWG 20-7)
Material: E-Cu, tin galvanised
Dimensional tolerance acc. to DIN 46228 sect. 4

General ordering data

| | |
|------------|--|
| Version | Wire-end ferrule, Standard, 13 mm, 10 mm, blue |
| Order No. | 9036220000 |
| Type | H2,5/16DS BL |
| GTIN (EAN) | 4032248068012 |
| Qty. | 500 items |
| Packaging | loose |

Technical data

Approvals

Approvals



| | |
|-------------------------|----------------------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (UR) | E354986 |
| Certificate no. (cULus) | E499744 |

Dimensions and weights

| | |
|------------|--------|
| Net weight | 0.16 g |
|------------|--------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Technical data

| | | | |
|------------------------|--|---------|----------|
| Description of article | Wire end ferrule with plastic collar, special size, blue | Version | Standard |
|------------------------|--|---------|----------|

Wire-end ferrules

| | | | |
|-------------------------------|---------------------|---|-------------|
| Contact surface diameter (D1) | 2.2 mm | Contact surface length (L2) | 10 mm |
| Collar diameter (D2) | 4.2 mm | Plastic collar thickness (S2) | 0.25 mm |
| L1 in mm | 16.00 mm | Wire connection cross section AWG, max. | AWG 14 |
| Metal sleeve thickness (S1) | 0.15 mm | Stripping length | 13 mm |
| Conductor cross-section | 2.5 mm ² | Colour code | Weidmueller |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000005 | ETIM 9.0 | EC000005 |
| ETIM 10.0 | EC000005 | ECLASS 14.0 | 27-40-02-01 |
| ECLASS 15.0 | 27-40-02-01 | | |

Drawing

