

CUTTER 20 A**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Cutting tools for conductors up to 8 mm, 12 mm, 14 mm and 22 mm outside diameter. The special blade geometry allows pinch-free cutting of copper and aluminium conductors with minimum physical effort. The cutting tools (KT 8 to KT 22) also come with VDE and GS-tested protective insulation up to 1,000 V in accordance with EN/IEC 60900.

General ordering data

Version	Cutting tool for one-hand operation
Order No.	9040140000
Type	CUTTER 20 A
GTIN (EAN)	4008190467098
Qty.	1 items

CUTTER 20 A

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	31 mm	Depth (inches)	1.2205 inch
Height	71.5 mm	Height (inches)	2.815 inch
Width	245 mm	Width (inches)	9.6456 inch
Net weight	443.7 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

Technical data

Description of article	Front cable cutter up to 20 mm cable diameters	Version	One-hand mechanical
------------------------	--	---------	---------------------

Cutting tools

Copper cable - solid, max. (AWG)	3 AWG	Copper cable - solid, max.	25 mm ²
Copper cable - flexible, max. (AWG)	3/0 AWG	Copper cable - flexible, max.	95 mm ²
Copper cable - stranded, max. (AWG)	1 AWG	Copper cable - stranded, max.	50 mm ²
Copper cable, max. diameter	22 mm	Data / telephone / control cable, max. Ø	22 mm
Single-core aluminium cable, max.(mm ²)	50 mm ²	Stranded aluminium cable, max. (AWG)	2/0 AWG
Stranded aluminium cable, max (mm ²)	70 mm ²	Stranded aluminium cable, max. diameter	22 mm

Classifications

ETIM 8.0	EC000142	ETIM 9.0	EC000142
ETIM 10.0	EC000142	ECLASS 14.0	21-04-47-01
ECLASS 15.0	21-04-47-01		