

**CRIMPER 2.5 I****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Crimping tools for insulated connectors  
cable lugs, terminal pins, parallel and serial connectors,  
plug-in connectors

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With stop for exact positioning of the contacts.
- Tested to DIN EN 60352 part 2

**General ordering data**

Version	Tools, Crimping tool for contacts, 0.5mm <sup>2</sup> , 2.5mm <sup>2</sup> , Trapezoidal crimp
Order No.	<a href="#">9040510000</a>
Type	CRIMPER 2.5 I
GTIN (EAN)	4008 19046 1478
Qty.	1 items
Delivery status	This article will no longer be available in the future.
Available until	2026-02-28T00:00:00+01:00

## CRIMPER 2.5 I

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Width	200 mm	Width (inches)	7.874 inch
Net weight	410 g		

## Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

## Technical data

Description of article	Crimping tool for insulated connectors, 0.5-2.5 mm <sup>2</sup>	Version	Mechanical, without interchangeable inserts
------------------------	-----------------------------------------------------------------	---------	---------------------------------------------

## Description of contact

Type of contact	Wire-end ferrules with/without plastic collars	Conductor cross-section, max. AWG	AWG 14
Conductor cross-section, min. AWG	AWG 20	Crimping range, max.	2.5 mm <sup>2</sup>
Crimping range, min.	0.5 mm <sup>2</sup>		

## tool data crimping

Drive	mechanical	Wire end ferrules cross-section, max.	2.5 mm <sup>2</sup>
Wire end ferrules cross-section, min.	0.5 mm <sup>2</sup>	Crimping type/profile	Trapezoidal crimp

## Classifications

ETIM 8.0	EC000168	ETIM 9.0	EC000168
ETIM 10.0	EC000168	ECLASS 14.0	21-04-38-11
ECLASS 15.0	21-04-38-11		