

## CRIMPER 16 Z

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Crimping tools for wire end ferrules, with and without plastic collars

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

### General ordering data

Version	Tools, Crimping tool for wire-end ferrules, 6mm <sup>2</sup> , 16mm <sup>2</sup> , Trapezoidal crimp
Order No.	<a href="#">9040540000</a>
Type	CRIMPER 16 Z
GTIN (EAN)	4008 19046 1447
Qty.	1 items

## CRIMPER 16 Z

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

Depth	30 mm	Depth (inches)	1.1811 inch
Height	78 mm	Height (inches)	3.0709 inch
Width	200 mm	Width (inches)	7.874 inch
Length	200 mm	Length (inches)	7.874 inch
Net weight	373.61 g		

### Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	2159813b-98fd-4068-b62a-bc89a046c012

### Technical data

Description of article	Crimping tool for wire-end ferrules 6 - 16mm <sup>2</sup>	Version	Mechanical, without interchangeable inserts
------------------------	---	---------	---

### Description of contact

Type of contact	Wire-end ferrules with/without plastic collars	Conductor cross-section, max. AWG	AWG 6
Conductor cross-section, min. AWG	AWG 10	Crimping range, max.	16 mm <sup>2</sup>
Crimping range, min.	6 mm <sup>2</sup>		

### tool data crimping

Drive	mechanical	Wire end ferrules cross-section, max.	16 mm <sup>2</sup>
Wire end ferrules cross-section, min.	6 mm <sup>2</sup>	Crimping type/profile	Trapezoidal crimp

### Classifications

ETIM 8.0	EC000168	ETIM 9.0	EC000168
ETIM 10.0	EC000168	ECLASS 14.0	21-04-38-11
ECLASS 15.0	21-04-38-11		