

STRIPPER 6**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

General ordering data

Version	Stripping and cutting tool
Order No.	9046240000
Type	STRIPPER 6
GTIN (EAN)	4032248298648
Qty.	1 items

STRIPPER 6**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com
Technical data**Dimensions and weights**

Depth	19 mm	Depth (inches)	0.748 inch
Height	87 mm	Height (inches)	3.4252 inch
Width	200 mm	Width (inches)	7.874 inch
Net weight	158.4 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

Technical data

Description of article	Stripping tool for wires up to 6 mm ² / with integrated cable cutter
------------------------	---

Stripping tools

Cable type	Flexible and solid conductors with PVC insulation	Stripping range AWG, max.	10 AWG
Stripping range AWG, min.	28 AWG	Stripping length, max.	20 mm
Conductor cross-section, max.	6 mm ²	Conductor cross-section, min.	0.08 mm ²

Classifications

ETIM 8.0	EC002109	ETIM 9.0	EC002109
ETIM 10.0	EC002109	ECLASS 14.0	21-04-37-06
ECLASS 15.0	21-04-37-06		