

## CA 100/6,0

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

### General ordering data

Version	Automatic machines, Automatic stripper and crimper
Order No.	<a href="#">9203520000</a>
Type	CA 100/6,0
GTIN (EAN)	4032248554799
Qty.	1 items

**Technical data**

**Approvals**

ROHS	Conform
------	---------

**Dimensions and weights**

Depth	400 mm	Depth (inches)	15.748 inch
Height	460 mm	Height (inches)	18.1102 inch
Width	530 mm	Width (inches)	20.8661 inch
Net weight	49000 g		

**Environmental Product Compliance**

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c, 7a, 7cI
REACH SVHC	Lead 7439-92-1

**PW65 maintenance - automatic stripping/crimping**

Stripping range	Only for 6,0 mm <sup>2</sup> wire end ferrule with collar	Drive	Electropneumatic
Pulse time	approx. 1.5 s	Crimping	Trapezoidal
Crimping length	12 - 18 mm	Consumables	loose cable lugs, With and without plastic collar
Compressed-air connection	5 bar	Electrical connection	100-240 V / 50/65 Hz

**Classifications**

ETIM 8.0	EC002778	ETIM 9.0	EC002778
ETIM 10.0	EC002778	ECLASS 14.0	17-13-01-01
ECLASS 15.0	17-13-01-01		