

COMBI CHECK 2MM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

The main function of the voltage tester is to establish if voltage is present. A 2-pole voltage tester is the only approved testing instrument that fulfils the requirements of work protection regulations.

- with LED-Display
- acc. to VDE standard
- high peak voltage strength
- the right tester for every application

General ordering data

Version	Testing tools, 2-pole voltage tester type 1156
Order No.	9204230000
Type	COMBI CHECK 2MM
GTIN (EAN)	4032248616497
Qty.	1 items
Delivery status	Discontinued
Available until	2021-01-31T00:00:00+01:00
Alternative product	VT COMBI PRO

COMBI CHECK 2MM

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Net weight	204 g
------------	-------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c, 7a, 7cl
REACH SVHC	Lead 7439-92-1

Technical data

Description of article	Voltage tester up to 690 V / 100 Hz LED
------------------------	---

Measuring and testing devices

Measuring range category	CAT III - 690V/ CAT IV - 400V	Rated voltage, max.	690 V AC/DC
Rated voltage, min.	6 V	AC voltage measuring range	6-690 V
DC voltage measuring range	690 V	Working temperature, max.	45 °C
Working temperature, min.	-15 °C	DC voltage display	6, 12, 24, 50, 120, 230, 400, 690 V
AC voltage display	6, 12, 24, 50, 120, 230, 400, 690 V	Frequency range, max.	100 Hz
Frequency range, min.	0 Hz	Display	LED
Protection degree	IP65	Battery type	1.5 V type AAA battery
Continuity test	Yes - visual + acoustic	Insulation test	6 kV
Peak voltage resistance	8 kV		

Classifications

ETIM 8.0	EC000494	ETIM 9.0	EC000494
ETIM 10.0	EC000494	ECLASS 14.0	27-20-03-08
ECLASS 15.0	27-20-03-08		