


RS 32 24VDC LD LP 2U

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Product image



General ordering data

Version	RS-SERIES, Relay module, Number of contacts: 2, CO contact AgNi 90/10, Rated control voltage: 24 V DC $\pm 10\%$, Continuous current: 4 A, Screw connection, Test button available: No
Order No.	9406121001
Type	RS 32 24VDC LD LP 2U
GTIN (EAN)	4008190027193
Qty.	10 items
Delivery status	Discontinued
Available until	2023-08-31T00:00:00+02:00
Alternative product	TRPL 24VDC 2CO

RS 32 24VDC LD LP 2U

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	63.5 mm	Depth (inches)	2.5 inch
Height	70 mm	Height (inches)	2.7559 inch
Width	25 mm	Width (inches)	0.9842 inch
Net weight	44.88 g		

Temperatures

Storage temperature	-40 °C...60 °C	Operating temperature	-25 °C...40
Humidity	40 °C / 93 % rel. humidity, no condensation		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	7a
REACH SVHC	Lead 7439-92-1
SCIP	7b5ffb72-271d-4c73-8b09-bd0aaee3697a

Control side

Rated control voltage	24 V DC \pm 10 %	Rated current DC	25 mA
Power rating	0.6 W	Status indicator	red LED
Protective circuit	Free-wheeling diode, Reverse polarity protection		

Load side

Rated switching voltage	250 V AC	Max. switching frequency at rated load	0.1 Hz
Max. switching voltage, AC	250 V	Inrush current	6 A
AC switching capacity (resistive), max.	1000 VA	Switch-on delay	< 13 ms
Switch-off delay	\leq 10 ms	Contact type	2 CO contact (AgNi 90/10)
Mechanical service life	30 x 10 ⁶ switching cycles	Min. switching power	1 mA @ 24 V, 10 mA @ 10 V, 100 mA / 5 V DC

General data

Version	soldered relay	Mounting rail	TS 32, TS 35
Test button available	No	Mechanical switch position indicator	No
Colour	orange		

Insulation coordination

Rated voltage	300 V	Pollution severity	2
Surge voltage category	III	Creepage and clearance distance input \rightarrow 3 mm output	

RS 32 24VDC LD LP 2U

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dielectric strength to mounting rail	4 kVeff / 1 Min.	Impulse withstand voltage	4 kV (1.2/50 µs)
Protection degree	IP20		

Connection data

Wire connection method	Screw connection	Stripping length, rated connection	8 mm
Clamping range, rated connection	2.5 mm ²	Clamping range, min.	0.5 mm ²
Clamping range, max.	4 mm ²		

Classifications

ETIM 8.0	EC001437	ETIM 9.0	EC001437
ETIM 10.0	EC001437	ECLASS 14.0	27-37-16-01
ECLASS 15.0	27-37-16-01		

Wiring diagram

