

## SAIL-VSB-M12G-20U


**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



Weidmüller can supply valve plugs as connecting lines with M8/M12 plugs and one end without connector. The status of the valve plug is shown by an LED. The valve plugs have a protective circuit. The Weidmüller range includes valve plugs of type A, B and C to DIN and industry standards. Protection class IP 67 is fulfilled when screwed in. The outlet direction is also a decisive factor, therefore Weidmüller offers different versions.

### General ordering data

|            |   |
|------------|---|
| Version    | Valve cable (assembled), Straight plug - valve plug, Industrial design B (11 mm), M12 = A-coded, Cable length: 20 m, PUR, black |
| Order No.  | <a href="#">9457682000</a>  |
| Type       | SAIL-VSB-M12G-20U   |
| GTIN (EAN) | 4050118369700   |
| Qty.       | 1 items   |

## SAIL-VSB-M12G-20U

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

## Dimensions and weights

Net weight 562.32 g

## Environmental Product Compliance

RoHS Compliance Status Compliant with exemption

RoHS Exemption (if applicable/known) 6c

REACH SVHC Lead 7439-92-1

SCIP e8d8af70-4c85-4483-bc8c-9bc5b598e2a9

## Technical specifications for cable

|                               |                           |                                  |                     |
|-------------------------------|---------------------------|----------------------------------|---------------------|
| Cable length                  | 20 m                      | Sheathing colour                 | black               |
| Suitable for cable carriers   | Yes                       | Core cross-section               | 0.5 mm <sup>2</sup> |
| Shielded                      | No                        | Halogen                          | No                  |
| Insulation                    | PP                        | Acceleration                     | 5 m/s <sup>2</sup>  |
| Bending radius, min., moving  | 10 x cable diameter       | Bending radius, min., stationary | 5 x cable diameter  |
| Bending cycles                | 2 Mio                     | Speed                            | 200 m/s             |
| Sheath material               | PUR                       | Welding spark resistance         | No                  |
| Colour coding                 | brown, blue, Green/yellow | Torsion resistance               | 0 °/m               |
| Temperature range, stationary | -50...80 °C               | Resistant to welding beads       | No                  |
| Temperature range, moving     | -25...80 °C               | Number of poles                  | 3                   |
| Outside diameter              | 4.6 mm ± 0.2 mm           |                                  |                     |

## General technical data

|                              |  |   |                            |
|------------------------------|--|---|----------------------------|
| Coding                       | Industrial design B (11 mm), M12 = A-coded | Contact surface                                     | tinned                     |
| LED                          | Yes  | Version   | Straight plug - valve plug |
| Nominal voltage              | 24 V                                       | Nominal current                                     | 4 A                        |
| Protection degree            | IP67, when screwed in                      | All valve plugs are fitted with protective circuits | Zener diode                |
| Temperature range of housing | -25...+80 °C                               |   |                            |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001855    | ETIM 9.0    | EC001855    |
| ETIM 10.0   | EC001855    | ECLASS 14.0 | 27-06-03-12 |
| ECLASS 15.0 | 27-06-03-12 |             |             |

**SAIL-VSB-M12G-20U**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Drawings**

**Dimensioned drawing**



**Dimensioned drawing**



**Pole scheme**



**Pole scheme**



**Wiring diagram**

