Data sheet

# SAIL-VSB-M12G-10U

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Weidmüller can supply valve plugs as connecting lines with M8/M12 plugs and one end without connector. The status of the valve plug is shown by an LED. The valve plugs have a protective circuit. The Weidmüller range includes valve plugs of type A, B and C to DIN and industry standards. Protection class IP 67 is fulfilled when screwed in. The outlet direction is also a decisive factor, therefore Weidmüller offers different versions.

## General ordering data

| | |
|---|---|
| Version | Valve cable (assembled), Straight plug - valve plug, Industrial design B (11 mm), M12 = A-coded, Cable length: 10 m, PUR, black |
| Order No. | 9457681000 |
| Type | SAIL-VSB-M12G-10U |
| GTIN (EAN) | 4032248229161 |
| Qty. | 1 items |
| Delivery status | This article will no longer be available in the future. |
| Last order date | 2027-02-28T00:00:00+01:00 |

# Data sheet

## SAIL-VSB-M12G-10U

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

# Technical data

### Approvals

| | |
|---|---|
| Approvals | |
| ROHS | Conform |

### Dimensions and weights

| | |
|---|---|
| Net weight | 333 g |

### Environmental Product Compliance

| | |
|---|---|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | e8d8af70-4c85-4483-bc8c-9bc5b598e2a9 |

### Technical specifications for cable

| | | | |
|---|---|---|---|
| Cable length | 10 m | Sheathing colour | black |
| Suitable for cable carriers | Yes | Core cross-section | 0.5 mm² |
| Shielded | No | Halogen | No |
| Insulation | PP | Acceleration | 5 m/s² |
| Bending radius, min., moving | 10 x cable diameter | Bending radius, min., stationary | 5 x cable diameter |
| Bending cycles | 2 Mio | Speed | 200 m/s |
| Sheath material | PUR | Welding spark resistance | No |
| Colour coding | brown, blue, Green/yellow | Torsion resistance | 0 °/m |
| Temperature range, stationary | -50...80 °C | Resistant to welding beads | No |
| Temperature range, moving | -25...80 °C | Number of poles | 3 |
| Outside diameter | 4.6 mm ± 0.2 mm | | |

### General technical data

| | | | |
|---|---|---|---|
| Coding | Industrial design B (11 mm), M12 = A-coded | Connection thread | Miscellaneous |
| Contact surface | tinned | LED | Yes |
| Version | Straight plug - valve plug | Contact material | CuZn |
| Nominal voltage | 24 V | Nominal current | 4 A |
| Protection degree | IP67, when screwed in | All valve plugs are fitted with protective circuits | Zener diode |
| Temperature range of housing | -25...+80 °C | Tightening torque | Mounting screw M3: 0.4 Nm, M12: 0.8 - 1.2 Nm |

### Classifications

| | | | |
|---|---|---|---|
| ETIM 8.0 | EC001855 | ETIM 9.0 | EC001855 |
| ETIM 10.0 | EC001855 | ECLASS 14.0 | 27-06-03-12 |
| ECLASS 15.0 | 27-06-03-12 | | |


# SAIL-VSB-M12G-10U

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany


www.weidmueller.com

## Drawings


### Dimensioned drawing





### Dimensioned drawing




### Pole scheme




### Pole scheme




### Wiring diagram

