

## POK MOPL 0808

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



The Klippon® POK enclosure range is made from a high-quality glass fibre reinforced polyester and is ideal for applications and environments where corrosion resistance, impact resistance and a high IP protection class are a requirement.

Key features of the extensive product range:

- Available in 17 sizes
- Two standard finishes (colours): grey (similar to RAL 7001 for industrial use) and black (similar to RAL 9011 for harsh environments, Ex)
- Cover with stainless steel screws in cross-head / slotted design
- Moulded gasket made of silicone or chloroprene
- Fixing holes outside the sealed area to ensure high ingress protection of IP66
- Impact resistance up to 7 Joules
- Mounting directly in the enclosure or using an internal mounting plate
- Direct wall mounting possible using fixing holes or mounting feet
- Fastening thread to attach mounting rails and plates
- Up to E60 fire rating dependent on the configuration
- Weidmüller can manufacture and supply this enclosure to match customer specifications - fitted with all necessary terminals and cable glands.

### General ordering data

Version	Klippon POK (polyester empty enclosure), Mounting plate, Height: 64 mm, Width: 69 mm, Depth: 1.5 mm, Basic material: Sheet steel, galvanized, galvanized, silver
Order No.	<a href="#">9510570000</a>
Type	POK MOPL 0808
GTIN (EAN)	4032248415274
Qty.	1 items

**Technical data**

**Approvals**

ROHS	Conform
------	---------

**Dimensions and weights**

Depth	1.5 mm	Depth (inches)	0.0591 inch
Height	64 mm	Height (inches)	2.5197 inch
Width	69 mm	Width (inches)	2.7165 inch
Mounting dimension - width	59 mm	Net weight	11 g

**Temperatures**

Operating temperature
-----------------------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**General information**

Material thickness	1.5 mm	Type of fixing	when screwed in
Surface finish	galvanized	Basic material	Sheet steel, galvanized

**Classifications**

ETIM 8.0	EC000213	ETIM 9.0	EC000213
ETIM 10.0	EC000213	ECLASS 14.0	27-40-06-39
ECLASS 15.0	27-40-06-39		