

VT

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The main function of the voltage tester is to establish if voltage is present. A 2-pole voltage tester is the only approved testing instrument that fulfils the requirements of work protection regulations.

- with LED-Display
- acc. to VDE standard
- high peak voltage strength
- the right tester for every application

General ordering data

Version	Testing tools, 2-pole voltage tester
Order No.	9918950000
Type	VT
GTIN (EAN)	403224840583 1
Qty.	1 items

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	55 mm	Depth (inches)	2.1654 inch
Height	21 mm	Height (inches)	0.8268 inch
Width	190 mm	Width (inches)	7.4803 inch
Length	190 mm	Length (inches)	7.4803 inch
Net weight	115 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant
RoHS Exemption (if applicable/known)	7cl
REACH SVHC	No SVHC above 0.1 wt%
SCIP	b05b5 122-6117-4cb0-b28c-df32f921fa36

Technical data

Description of article Voltage tester from 12 – 690 V

Measuring and testing devices

Load switchable	No	Measuring range category	CAT III 600 V, CAT IV 300 V
Rated voltage, max.	690 V AC/DC	Rated voltage, min.	12 V AC/DC
AC voltage measuring range	12-690 V	DC voltage measuring range	1000 V
Working temperature, max.	55 °C	Working temperature, min.	-15 °C
DC voltage display	12, 50, 120, 230, 400, 690 V	AC voltage display	12, 50, 120, 230, 400, 690 V
Frequency range, max.	65 Hz	Frequency range, min.	0 Hz
Display	LED	Protection degree	IP64
Phase sequence display	No	Continuity test	No
Insulation test	5 kV	Peak voltage resistance	5 kV
Tested and approved according to	EN/IEC 61010, EN 61243-3 2010	Test probe protection GS 38	No
Test probe illumination	No	HOLD function	No

Classifications

ETIM 8.0	EC000494	ETIM 9.0	EC000494
ETIM 10.0	EC000494	ECLASS 14.0	27-20-03-08
ECLASS 15.0	27-20-03-08		

