

DC SB M 50A 4POL EVO 1 KV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Dati generali per l'ordinazione**

Versione	Fotovoltaico, Interruttore, Interruttore sezionatore, 1000 V, Versione DC, 50 A, 4 poli, Interruttore manuale
N. d'ordine	3123820000
Tipo	DC SB M 50A 4POL EVO 1 KV
GTIN (EAN)	4099987272032
CPZ	1 Pieza

DC SB M 50A 4POL EVO 1 KV

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Dati tecnici

Omologazioni

ROHS	Conforme
------	----------

Dimensioni e pesi

Profondità	121.5 mm	Profondità (pollici)	4.7835 inch
Posizione verticale	165 mm	Altezza (pollici)	6.4961 inch
Larghezza	140 mm	Larghezza (pollici)	5.5118 inch
Peso netto	702 g		

Temperature

Temperatura ambiente	-30 °C...50 °C
----------------------	----------------

Conformità ambientale del prodotto

Stato conformità RoHS	Conforme senza esenzione
REACH SVHC	No SVHC superiori a 0,1 wt%

Dati generali

Grado di protezione	IP65
---------------------	------

Classificazioni

ETIM 8.0	EC000216	ETIM 9.0	EC004830
ETIM 10.0	EC004830	ECLASS 14.0	27-07-02-03
ECLASS 15.0	27-07-02-03		

Testi descrittivi per l'offerta

Testo bando lungo	Load break switch in polyester housing. Suitable for switching off the DC side. Number of poles: 4 Operating current, rated value (Ie): - according to IEC (PV1, 1000 V): 50 A - according to IEC (PV1, 1500 V): 20 A - according to IEC (PV2, 1000 V): 20 A - according to IEC (PV2, 1500 V): 8 A Rated insulation voltage (Ui): - according to IEC: 1500 V Suitability for use: Main switch: Yes Number of contacts normally open: 4 Number of contacts normally closed: 0 Number of switching positions: 2 Lockable: Yes The switch is mounted using 4 screws.
-------------------	--

DC SB M 50A 4POL EVO 1 KV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Dati tecnici**

Protection class (IP): 65
Polyester housing with
connection via MC4-Evo
2 connector, compatible
with cable type TÜV 2
Pfg 1169/08.07 / EN
50618:2063
Dimensions HxWxD:
235x140x121.5 mm.
Approval according to low
voltage switchgear and
controlgear IEC 60947-3,
DIN VDE 0660 Part 107
(EN 60947-3)

Disegni

