


ZB 35K GE/GN M6X16

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

제품 이미지



바이드물러는 다양한 유형의 버스바 시스템을 위한 태핑 터미널을 제공합니다. 응용 분야에 따라 절연 및 비절연 탭오프 단자대를 구분할 수 있습니다.

일반 주문 데이터

버전	단자대 (버스바 결선)
주문 번호	0502660000
유형	ZB 35K GE/GN M6X16
GTIN (EAN)	4008190052294
수량	20 items

기술 데이터

승인

승인



ROHS	준수
UL File Number Search	UL 웹사이트
인증 번호(UR)	E60693

치수 및 중량

깊이	34 mm	깊이 (인치)	1.3386 inch
높이	32 mm	높이 (인치)	1.2598 inch
너비	14 mm	폭 (인치)	0.5512 inch
순중량	18.67 g		

온도

주변 온도	-5 °C...40 °C
-------	---------------

환경 제품 규정 준수

RoHS 준수 상태	준수, 예외 미존재
REACH SVHC	0.1 wt% 이상의 SVHC 없음

CSA 등급 데이터

와이어 단면적 최대(CSA)	2 AWG	인증 번호(CSA)	12400-237
와이어 단면적 최소(CSA)	6 AWG		

UL 등급 데이터

컨덕터 크기 팩토리 결선 최대(UR)	2 AWG	컨덕터 크기 팩토리 결선 최소(UR)	6 AWG
인증 번호(UR)	E60693	컨덕터 크기 필드 결선 최소(UR)	6 AWG
컨덕터 크기 필드 결선 최대(UR)	2 AWG		

등급 데이터

정격 단면적	35 mm ²
--------	--------------------

시스템 사양

버전	10 x 3 mm 버스바용
----	----------------

일반

설치 권고	간선 관통(부싱)
-------	-----------

자재 데이터

기본 재질	스틸	절연재	PA
컬러 코드	녹색/노란색		

ZB 35K GE/GN M6X16

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

기술 데이터

정격 데이터 IECEx/ATEX

인증 번호(ATEX)	DEMKO03ATEX136028U	인증 번호(IECEX)	IECEXULD13.0005U
와이어 단면적 최대(ATEX)	35 mm ²	와이어 단면적 최대(IECEX)	35 mm ²
마킹 EN 60079-7	Ex eb II C Gb	Ex 2014/34/EU 라벨	II 2 G D
안전 관련 주의 사항	<p>Installation instructions: The potential equalisation (PE) rail modules are suitable for use in housings in atmospheres with flammable gases and dust. For use in areas with flammable gases, these housings must meet the requirements of EN 60079-0 and EN 60079-7. For use in areas with flammable dust, these housings must meet the requirements of EN 60079-0 and EN 60079-31. When combined with other terminal block ranges and sizes, and when other accessories are used, you must comply with the clearance and creepage distances given. Regarding accessory use, the manufacturer's instructions must be followed. List of restrictions: The PE rail modules are considered one component, with Ex marking when used with the busbar holders of type SH and WEW. When used independently, the above named components are not covered by this certificate.</p>		

추가 기술 데이터

설치 권고	간선 관통(부싱)	장착 유형	스크류
-------	-----------	-------	-----

크기

TS 35 오프셋	39 mm
-----------	-------

클램프용 컨덕터(정격 결선)

조임 토크, 최대	5 Nm	조임 토크, 최소	2.5 Nm
탈피 길이	19 mm	결선 유형	클램프 요크
클램프 범위, 최대	35 mm ²	클램프 범위, 최소	16 mm ²
클램프 스크류	M 6	와이어 결선 단면적, 와이어 종단 페룰 DIN 46228/1 채용 가능 꼬임, 최대	35 mm ²
와이어 결선 단면, 가는 꼬임, 최대	35 mm ²	와이어 결선 단면, 가는 꼬임, 최소	16 mm ²
결선 단면적, 꼬임, 최소	16 mm ²	와이어 결선 단면적, 경질 코어, 최대	16 mm ²
와이어 결선 단면적, 경질 코어, 최소	16 mm ²		

기술 데이터

분류

ETIM 8.0	EC000001	ETIM 9.0	EC000001
ETIM 10.0	EC000001	ECLASS 14.0	27-25-01-16
ECLASS 15.0	27-25-01-16		