

QL 2 SAKK4

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

General ordering data

Version	Cross-connector (terminal), when screwed in, grey, 32 A, Number of poles: 2, Pitch in mm (P): 8.00, Insulated: No, Width: 13.9 mm
Order No.	9502540000
Type	QL 2 SAKK4
GTIN (EAN)	4008 190550530
Qty.	100 items

QL 2 SAKK4

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	1 mm	Depth (inches)	0.0394 inch
Height	6 mm	Height (inches)	0.2362 inch
Width	13.9 mm	Width (inches)	0.5472 inch
Net weight	0.52 g		

Temperatures

Storage temperature -25 °C...55 °C Ambient temperature -5 °C...40 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
REACH SVHC No SVHC above 0.1 wt%

Material data

Basic material Copper Colour grey

System specifications

Version Cross-connector

Additional technical data

Type of fixing when screwed in Installation advice Direct mounting
Explosion-tested version No Type of mounting when screwed in

Dimensions

Pitch in mm (P) 8.00 mm

General

Number of poles 2 Installation advice Direct mounting

Rating data

Nominal current 32 A

Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		