

**VH 13.5/4.9/3.3 NI****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

**General ordering data**

Version	Connecting sleeve (terminal), when screwed in, Width: 4.9 mm, Height: 13.5 mm, Depth: 4.9 mm, Number of poles: 1, Cu Zn
Order No.	<a href="#">9502580000</a>
Type	VH 13.5/4.9/3.3 NI
GTIN (EAN)	4008 190550578
Qty.	100 items

**Technical data**

**Approvals**

ROHS	Conform
------	---------

**Dimensions and weights**

Depth	4.9 mm	Depth (inches)	0.1929 inch
Height	13.5 mm	Height (inches)	0.5315 inch
Width	4.9 mm	Width (inches)	0.1929 inch
Net weight	1.17 g		

**Temperatures**

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Material data**

Basic material	Cu Zn	Colour	grey
----------------	-------	--------	------

**System specifications**

Version	for cross-connection link
---------	---------------------------

**Additional technical data**

Type of fixing	when screwed in	Installation advice	Direct mounting
Explosion-tested version	No		

**General**

Number of poles	1	Installation advice	Direct mounting
-----------------	---	---------------------	-----------------

**Classifications**

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		