

POK MOPL 1212

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The Klippon® POK enclosure range is made from a high-quality glass fibre reinforced polyester and is ideal for applications and environments where corrosion resistance, impact resistance and a high IP protection class are a requirement.

Key features of the extensive product range:

- Available in 17 sizes
- Two standard finishes (colours): grey (similar to RAL 7001 for industrial use) and black (similar to RAL 9011 for harsh environments, Ex)
- Cover with stainless steel screws in cross-head / slotted design
- Moulded gasket made of silicone or chloroprene
- Fixing holes outside the sealed area to ensure high ingress protection of IP66
- Impact resistance up to 7 Joules
- Mounting directly in the enclosure or using an internal mounting plate
- Direct wall mounting possible using fixing holes or mounting feet
- Fastening thread to attach mounting rails and plates
- Up to E60 fire rating dependent on the configuration
- Weidmüller can manufacture and supply this enclosure to match customer specifications - fitted with all necessary terminals and cable glands.

General ordering data

| | |
|------------|---|
| Version | Klippon POK (polyester empty enclosure), Mounting plate, Height: 107 mm, Width: 109 mm, Depth: 1.5 mm, Basic material: Sheet steel, galvanized, Miscellaneous, silver |
| Order No. | 9510590000 |
| Type | POK MOPL 1212 |
| GTIN (EAN) | 4008190498221 |
| Qty. | 1 items |

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|-----------------------------|--------|----------------------------|-------------|
| Depth | 1.5 mm | Depth (inches) | 0.0591 inch |
| Height | 107 mm | Height (inches) | 4.2126 inch |
| Width | 109 mm | Width (inches) | 4.2913 inch |
| Mounting dimension - height | 52 mm | Mounting dimension - width | 95 mm |
| Net weight | 119 g | | |

Temperatures

| |
|-----------------------|
| Operating temperature |
|-----------------------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

General information

| | | | |
|--------------------|---------------|----------------|-------------------------|
| Material thickness | 1.5 mm | Type of fixing | when screwed in |
| Surface finish | Miscellaneous | Basic material | Sheet steel, galvanized |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000213 | ETIM 9.0 | EC000213 |
| ETIM 10.0 | EC000213 | ECLASS 14.0 | 27-40-06-39 |
| ECLASS 15.0 | 27-40-06-39 | | |